



Hach 934-AH Filters, 110mm, 100/pk

Αρ. προϊόντος:

2511211

EUR Τιμή:

Επικοινωνήστε μαζί μας

Δεν εμφανίζεται η ημερομηνία αποστολής

Hach 934-AH Filters are specified for use in Standard methods 2540 C, 2540 D and 2540 E. Fast flow rate, fine porosity and 1.5 µm particle retention have made this binderless borosilicate glass microfiber filter the accepted industry standard for over 50 years. Hach 934-AH Filters can withstand temperatures over 500°C, which is a unique and especially important feature for laboratories performing Fixed and Volatile Suspended Solids analysis of water and wastewater.

The trademark 934-AH is owned by GE Healthcare/Whatman Inc. and used under exclusive license for purposes of private label.

Προδιαγραφές

Διάμετρος :	110 mm
Μέγεθος πόρου :	1.5 µm
Μονάδες μέτρησης:	100/pk
Όγκος/Μέγεθος πακέτου :	100 /pk
Υλικό :	Glass Microfiber