



Replacement salt bridge for pH sensor, outer-junction, PPS Salt Bridge, PVDF

Αρ. προϊόντος:

SB-R1SV

Επικίνδυνο

EUR Τιμή:
Διαθέσιμο

Επικοινωνήστε μαζί μας



Lowens Lifetime Cost of Process pH Sensors

The double junction salt bridge on all Hach pHDTM Differential pH / ORP Sensors is field-replaceable, and includes a FKM/FPM O-ring. Salt bridges are shipped in a salt solution to prevent dehydration / dry-out and can be stored in the shipping solution until needed. Salt bridges are available in a variety of materials and pre-packaged quantities.

Προδιαγραφές

Ειδικές σημειώσεις :

Each salt bridge has a ceramic inner junction, FKM/FPM O-ring, and contains binary, equi-transferrant fill solution. (Salt bridges are shipped in a salt solution.)

Υλικό :

PPS