



Acidification/Cleaning Unit for Amperometric Sensors

Αρ. προϊόντος:

LZY051

EUR Τιμή:

Επικοινωνήστε μαζί μας

Αποστολή εντός 2 εβδομάδων

Many amperometric processes have optimal pH ranges in which they will be most accurate and produce the best results. Adding an acidification/cleaning unit onto instruments such as the CL10 sc can help to ensure that samples stay range that is favorable for measurement.

Προδιαγραφές

Depth panel:	107 mm
Height (panel):	270 mm
Width:	250 mm
Απαίτηση Ισχύος (Voltage):	12 V DC
Εγγύηση :	24 μήνες
Κατηγορία ασφάλειας :	T, 250 mA, 250V
Μήκος καλωδίου :	1 m digital
Όγκος :	10 L chemicals not supplied
Παροχή :	Min 0.24, max. 1 mL/min
Σύνδεση διεργασίας :	0.125 " NPT (for tube fittings)
Τι περιέχει το καλάθι:	Acidification Unit, Carboy, 1 M digital extension cable, Tubing Kit, and Instructions.
Υλικό :	Carboy: PEHD (high-density polyethylene)

Τι περιέχει το καλάθι

Acidification Unit, Carboy, 1 M digital extension cable, Tubing Kit, and Instructions.