



POCKET Colorimeter II Fixed wavelength 600 nm

Αρ. προϊόντος:

5870060

ΚΑΤΑΡΓΗΜΕΝΟ ΣΤΟΙΧΕΙΟ

Αυτό το στοιχείο δεν είναι πλέον διαθέσιμο.

Small in size, big on waterproof analysis

Rugged and reliable wavelength-specific Filter Photometer, 600 nm. User-programmable. In carrying case, complete with batteries, cuvettes and operating instructions.

Generic POCKET Colorimeter II Instruments are intended for applications not included in standard analysis systems. They are available in a range of wavelengths appropriate for many custom calibrations. In addition to the factory absorbance calibration (0-2.5 A), the instruments offer two user-entered, two-point, linear calibrations, and provide a choice of either 0.00 to 2.55 or 0.0 to 99.0 for the display value.

Simple: all functions are available via only four keys

Power: battery operation for a maximum of 2000 tests

Clear readings: even under difficult conditions, thanks to backlit display and large readout

Reliable results with no mains connection

Rugged construction yet lightweight

Προδιαγραφές

Lamp Type:	Light Emitting Diode (LED)
Ανιχνευτής :	Silicon detector
Βάρος :	0,23 kg
Διαστάσεις (ΥxΠxB):	155 mm x 61 mm x 35 mm
Κατάταξη περιβλήματος :	IP67 (εκτός από το χώρο τοποθέτησης μπαταριών)
Μήκος κύματος :	Fixed wavelength ± 2 nm varies with model
Οθόνη:	LCD, backlit
Οπτική διαδρομή κυψελίδας δείγματος :	1 cm 25 mm
Παράμετρος :	Wavelength specific, 600 nm
Πιστοποιήσεις συμμόρφωσης:	European CE mark
Τι περιέχει το καλάθι:	Each wavelength specific Pocket Colorimeter II Instrument comes complete as a ready-to-use kit in a sturdy custom carrying case, including a printed manual.

Τι περιέχει το καλάθι

Each wavelength specific Pocket Colorimeter II Instrument comes complete as a ready-to-use kit in a sturdy custom carrying case, including a printed manual.