



Desiccator, Vacuum

Αρ. προϊόντος:

2088800

EUR Τιμή:

Επικοινωνήστε μαζί μας

Δεν εμφανίζεται η ημερομηνία αποστολής

Round polycarbonate cover and polypropylene base create implosion-proof chamber at full vacuum. Chamber is impervious to alkali and acidic conditions. Recessed rim prevents grease (not included) from contacting bench surfaces when removed and eliminates need for a separate gasket. This vacuum model features leak-proof stopcock. Dimensions (height x diam): 245 mm x 330 mm (9.7" x 13"). Holds 454 g (1 lb) of dessicant. Ceramic dessicator plate (sold separately) is inert, non-stick, and corrosion resistant. Quadrants crafted into plate for easy tracking of material locations. Plate diameter: 230 mm (9").

Προδιαγραφές

Όγκος/Μέγεθος πακέτου :

1 each