



EZ5010 Calcium Hardness + Total Alkalinity Analyser

Αρ. προϊόντος:

EZ5010.XXXXXXXXXX

EUR Τιμή:

Επικοινωνήστε μαζί μας

Online automatic titration of Calcium Hardness + Total Alkalinity in water

EZ5000 Series Analysers are multi-parameter titrators that achieve excellent precision and accuracy. Depending on the parameter of interest, the measuring range and the water matrix the EZ5000 Series may use either potentiometry i.e. acid-base, redox or precipitation titration, where the endpoint is determined by a change in a specific variable, or photolorimetry, where colour change is used to determine the endpoint of the titration. The high precision dispenser for addition, robust peristaltic pumps for sampling and drain, and carefully designed liquid pathways all add up to the highest performance for industrial and environmental analysis needs.

Results you can rely on

Smart automatic features for validation, priming and cleaning are embedded in the controller software and contribute to analytical performance, maximised uptime and negligible operator intervention. Sample lines and analysis vessel are cleaned with demineralised water to eliminate cross contamination between samples. Electronic and wet-chemical part of the analyser are strictly separated. A transparent door allows for instant visual inspection of the wet part.

Flexibility that meets your needs

EZ Series Alkalinity and Hardness Analysers come in an attractive, ergonomic mainframe with a compact footprint. All hardware is controlled by the integrated industrial panel PC. The modular build allows for the analyser to match your application and operational needs.

- The standard measuring range can be narrowed by a different calibration range or extended via internal dilution options.
- Analogue and digital output options
- Multiple stream analysis for up to 8 sample streams

There are many additional options available. Please contact Hach for more details.

Προδιαγραφές

Demineralised water:	For rinsing
Digital outputs:	Optional: Modbus (TCP/IP, RS485)
Earth connection:	Dry and clean earth pole with low impedance (< 1 Ohm) using an earth cable of > 2.5 mm ²
Instrument air:	Dry and oil free according to ISA-S7.0.01-1996 quality standard for instrument air
Precision:	Better than 2% full scale range for standard test solutions
Reagent Requirements:	Keep between 10 - 30 °C

Validation:	Automatic; frequency freely programmable
Αναλογικές έξοδοι:	Active 4 - 20 mA max. 500 Ohm load, standard 1, max. 8 (option)
Αποστράγγιση :	Ατμοσφαιρική πίεση, με εξαερισμό, ελάχιστη διάμετρος 32 mm
Αριθμ. Ροών δείγματος :	1, 2, 4 or 8
Βαθμονόμηση :	N.A.
Βαθμός προστασίας:	Protection class: Analyser cabinet: IP44 / Panel PC: IP65
Βάρος :	25 kg
Δείγμα: πίεση:	By external overflow vessel
Διαστάσεις (ΥxΠxB):	690 mm x 465 mm x 330 mm
Εγγύηση :	24 μήνες
Εύρος μέτρησης :	Ca: 10 - 100 mg/L CaCO_3 ; Alk: 20 - 500 mg/L CaCO_3
Θερμοκρασία Δείγματος:	10 - 30 °C
Θερμοκρασία περιβάλλοντος :	10 - 30 °C $\pm$ 4 °C deviation at 5 - 95% relative humidity (non-condensing)
Μέθοδος μέτρησης :	Acid-base titration (alkalinity only); Calmagite EDTA titration with LED dipping probe (combined)
Όνομα μεθόδου :	Titrimetric
Όριο ανίχνευσης :	Calcium Hardness: $\leq$ 10 mg/L Total Alkalinity: $\leq$ 20 mg/L
Παράμετρος :	Calcium Hardness; Total Alkalinity
Παρεμποδισείς :	Hardness: Some metal ions interfere by causing fading or indistinct end points or by stoichiometric consumption of EDTA. Suspended or colloidal organic matter also may interfere with the end point. Large amounts of colour and turbidity interferes. Fats, oil, proteins, surfactants and tar. Alkalinity: Soaps, oily matter, suspended solids or precipitates may coat the glass electrode and cause a sluggish response. Allow additional time between titrant additions to let the electrode come to equilibrium or clean the electrodes occasionally.
Πιστοποιήσεις :	CE compliant / UL certified
Ποιότητας δείγματος :	Maximum particle size 100 μm , < 0.1 g/L; Turbidity < 50 NTU
Ρυθμός ροής δείγματος :	100 - 300 mL/min
Συναγερμός :	1 x malfunctioning, 4 x user-configurable, max. 24 VDC/0.5 A, potential free contacts
τροφοδοσία :	100 - 240 VAC, 50/60 Hz Max. power consumption: 120 VA
Υλικό :	Hinged part: Thermoform ABS, door: PMMA Wall section: Galvanised steel, powder coated
Χρόνος κύκλου:	20 - 30 minutes 40 minutes (+ Total Hardness Ca)