



H₂S Calibration Gas Regulator, GS1440/GS2440EX

Αρ. προϊόντος:

LXZ449.99.00023

EUR Τιμή:

Επικοινωνήστε μαζί μας

Διαθέσιμο

This gas regulator contains non-gas equipment required for on-site calibration of the GS1440/GS2440EX sensor (measurement range 0 - 1000 ppm or 0 - 5 mg/L), including a flow regulator and a calibration cap.

Προδιαγραφές

Τι περιέχει το καλάθι:

Includes non-gas equipment required for on-site calibration of the GS1440/GS2440EX sensor.

Please note that the 1000 ppm H₂S calibration gas (LCX449) required for the sensor calibration must be purchased separately.

Τι περιέχει το καλάθι

Includes non-gas equipment required for on-site calibration of the GS1440/GS2440EX sensor. Please note that the 1000 ppm H₂S calibration gas (LCX449) required for the sensor calibration must be purchased separately.

Απαιτούμενα παρελκόμενα

- H₂S Calibration Gas, 1000 ppm, GS1440/GS2440EX (Item LCX449)